

FC Series Humidifiers

Consistent Humidification for High-Flow Applications

Perma Pure FC Series humidifiers use an exclusive Nafion™ membrane tubing to continuously humidify gas streams. These humidifiers operate over a wide range of flow rates and can use either liquid water or a humid gas stream as a source of humidity.

Key Features


- Humidifies continuously
- Transfers only water vapor
- Self-regulating
- High level of humidification

- Maintenance-free operation
- No moving parts
- Excellent corrosion resistance
- Humidifies high flow rates

Principle of Operation


Perma Pure's FC Series gas humidifiers are tubein-shell humidity exchangers that transfer heat and water vapor between two gas streams. They may operate as either water-to-gas or gas-to-gas humidity exchangers.

Water-to-gas humidifiers have liquid water on one side of the tube wall and a dry gas on the other. This arrangement offers the greatest amount of humidification; however, the reaction of the water molecules moving through the tubing wall absorbs heat. To counter this cooling effect, the inlet water must be heated. Hot, circulated deionized water should be used to optimize performance.



Gas-to-gas humidifiers use counter-flowing wet

and dry gas streams to move heat and humidity from one stream to the other. These units are energy efficient, as they do not require any additional power or heat. When gas passes inside the Nafion™ tubing, water is absorbed by and moves through the walls of the tubing. The movement of water is driven by the humidity gradient between the inside and outside of the tubing. Since only water molecules move through the tubing walls, liquid water is prevented from becoming entrained in the gas stream.



Model	Α		В		С		D	Port Sizes	Operating Fluid Pressure Range	
	inches	mm	inches	mm	inches	mm	inches	inches	kPa	psig
FC100-80	8.8	223	?	?	5.4	135	1.3	1/4 air inlet 1/8 wet stream	0 to 35 @ 80°C (176°F)	0 to 5 @ 80°C (176°F)
FC125-240-5MP	7.9	200.7	5	127	4.6	116.8	2.5	1/2	0 to 172 @ 80°C (176°F)	0 to 25 @ 80°C (176°F)
FC125-240-7MP	9.9	251.5	7	177.8	6.6	167.6				
FC125-240-10MP	12.9	327.7	10	254	9.6	243.8				
FC150-480-7PP	11.5	292.1	7	177.8	6.75	171.5	3.5	3/4	0 to 172 @ 80°C (176°F)	0 to 25 @ 80°C (176°F)
FC150-480-10PP	14.5	368.3	10	254	975	247.7				
FC150-480-15PP	19.5	495.3	15	381	14.75	374.7				
FC200-780-7MP	11.1	281.9	7	177.8	6.16	156.5	3.52	?	?	?
FC200-780-10MP	14.1	358.1	10	254	7.16	181.9				
FC300-1660-7LP	12.1	307.3	7	177.8	5.6	142.2				
FC300-1660-10LP/ HP	15.1	383.5	10	254	8.6	218.4	5.2	1 1/2	?	?
FC300-1660-15LP	20.1	510.5	15	381	13.6	345.4				
FC400-2500-7LP/HP	12.8	325.1	7	177.8	5.0	127	6.11	1 (2 optional)	?	?
FC400-2500-10LP	15.8	401.3	10	254	8.0	203.2				
FC600-7000-7PP	14.75	374.7	7	177.8	5.75	146.1	8.5	2	0 to 35 @ 80°C (176°F)	0 to 5 @ 80°C (176°F)
FC600-7000-10PP	17.75	450.9	10	254	8.75	222.3				
FC600-7000-15PP	22.75	577.9	15	381	13.75	349.3				

ETA Process Instrumentation

www.etapii.com sales@etapii.com tel 978.532.1330

Martech Controls

www.martechcontrols.com sales@martechcontrols.com tel: 315.876.9120